



SFH 7050 BioMon® Health Monitoring Ecol

ILE-BI01-GRIR-SC201.

Product Overview

At the heart of each BioMon® Eco1 is a BioMon SFH 7050 sensor for automatic fitness tracking from Osram Opto Semiconductors. The emitters may be individually controlled, so that the sensor can be used for various applications. Green light has been established as the best option for the pulse measurements on the wrist. Red or infrared emitters are generally preferred for pulse measurement on the finger, because they can also measure the oxygen content of the blood (pulse oximetry). In combination with the photodiode, the infrared LED can also be used as a proximity sensor. Eco1s are compact, powerful LED light sources built on FR4 with thermal vias for optimal thermal management. BioMon® Eco1s generate very little heat and therefore do not require any secondary Heat Sinking.



Applications

- Heart Rate Monitoring
- Pulse Oximetry
- Proximity Sensor

Technical Features

- BioMon® Eco1s contain a BioMon® SFH 7050 Sensor*
- Mounting holes using M3 screws allows easy installation
- Size (LxWxH): 20.25x13.70x0.90mm

Important Information and Precautions

- The BioMon® Eco1's LED, when powered up, is very bright. Thus it is advised that you do not look directly at it. Turn the Eco1 away from you and do not shine into the eyes of others.
- Do not operate BioMon[®] Eco1's with a Power Supply with unlimited current. Connection to constant voltage Power Supplies that are not current limited may cause the Eco1 to consume current above the specified maximum and cause failure or irreparable damage.
- The Eco1 board is a DOUBLE sided board for ease of connections, please ensure that one side is insulated to avoid shorting.
- DO NOT HOT PLUG ON LED SIDE OF POWER SUPPLY.
- DO NOT TOUCH or PUSH on the LED as this can cause irreparable damage.



IGS Version V1.1 November 2016

^{*}This datasheet should be read in conjunction with the relevant OSRAM Opto Semiconductors data on the LED used

Product Options


| ILS PART NUMBER | Colour | Relevant OSRAM LED Data |
|----------------------|--|-------------------------|
| ILE-BI01-GRIR-SC201. | Please consult the relevant OSRAM Datasheet for further information on Parameters of the BioMon® | SFH 7050 |

Minimum and Maximum Ratings

| ILS PART NUMBER | Operating Temperature [°C] | Storage Temperature [°C] |
|----------------------|----------------------------|--------------------------|
| ILE-BI01-GRIR-SC201. | -4085°C | -4085°C |


Directional Characteristics of Detector

Radiation characteristics of the Green, Red and IR Emitters



Radiation characteristics of the Green, Red and IR Emitters

Technical Drawing with cables (mm)



3D drawing files are available on request from ILS. Please call or email

© IGS Version V1.1 November 2016

© IGS Version V1.1 November 2016

www.i-led.co.uk

Pin Configuration

| Name | Function |
|------|----------------------|
| GC | Green LED Cathode |
| GA | Green LED Anode |
| RA | Red LED Anode |
| PA | Photodiode Anode |
| PC | Photodiode Cathode |
| RC | Red LED Cathode |
| IA | Infrared LED Anode |
| IC | Infrared LED Cathode |

BioMon® Eco1 Lens and Reflector Options

LEDIL precision-engineered Lenses and Reflectors allow for rapid deployment of all types of light fixtures, including street lights, wall-wash, high-bay, sconces, emergency beacons, parking garage/low-bay, MR and AR down lights and dock lights. Precision-engineered for maximum efficiency and durability, LEDIL Lenses and Reflectors are released alongside the latest product releases from our LED suppliers. You select the best LED for the application; choose LEDIL and you're selecting the best optical solution as well.

Currently there are not any recommend Lens options from LEDIL for the BioMon®, however physical locater pins for a number of Ledil product families are on the board. In-house Lux testing with a number of these has shown minimal losses. Due to the nature of the device, colour over beam consistency may be an issue for some applications. Beam angle

BioMon® Eco1 Heat Sink Options

information is not currently available.

ILS has a series of Aluminium Alloy Heat Sinks to be used with our standard range of LED Engines. These Heat Sinks are supplied with fixing screws for the light engine and for fixing to a base plate. They also come with Thermal Interface Material (TIM) attached to the top surface. Available in Black, Red, Silver and Blue colour variants. More versions will be introduced over the coming months and we are also happy to manufacture custom Heat Sinks to your request. This product would normally not require Heat Sinks as heat generated is normally minimal.

Thermal Interface Material Options

ILS have produced a range of high-performance, cost effective Thermal Interface Materials to match perfectly their standard products.

Our product fills the air pockets between the two surfaces, forming a continuous layer to conduct heat away from the LED to the Heat Sink.

As the Eco1 generates little heat, TIM is therefore not needed. Our double sided thermal tape would be suitable for fixing the Eco1 to a fixture, Heat Sink and flat substrate.

© IGS Version V1.1 November 2016

www.i-led.co.uk

Assembly Information

 In order to optimise the thermal management, the metal surface needs to be clean (dirt and oil free) and planar for the best contact with the LED module. A thermal grease or heat transfer material is highly recommended.

Safety Information

- The LED module itself and all its components must not be mechanically stressed.
- Assembly must not damage or destroy conducting paths on the circuit board.
- The mounting of the module is carried out by attaching it at the mounting holes. Metal mounting screws must be
 insulated with synthetic washers to prevent circuit board damage and possible short circuiting.
- To avoid mechanical damage to the connecting cables, the boards should be attached securely to the intended substrate. Heavy vibration should be avoided.
- Observe correct polarity!
- Depending on the product, incorrect polarity will lead to emission of red or no light. The module can be destroyed!
- Pay attention to standard ESD precautions when installing the BioMon® Eco 1.
- The BioMon® Eco 1, as manufactured, have no conformal coating and therefore offer no inherent protection against corrosion.
- Damage by corrosion will not be accepted as a materials defect claim. It is the user's responsibility to provide suitable protection against corrosive agents such as moisture and condensation and other harmful elements.
- For outdoor usage, housing is definitely required to protect the board against environmental influences. The design of the housing must correspond to the IP standards in the application. It is also the responsibility of the user to ensure any housing or modifications keep the Tc junction temperature to within stated ranges.
- To also ease the luminaire/installation approval, electronic control gear for LED or LED modules should carry the CE mark and be ENEC certified. In Europe the declarations of conformity must include the following standards: CE: EC z 61374-2-13, EN 55015, IEC 61547 and IEC 61000-3-2 ENEC: 61374-2-13 and IEC/EN 62384.
- The evaluation of eye safety occurs according to the standard IEC 62471:2006 ("photobiological safety of lamps and lamp systems"). Within the risk grouping system of this CIE standard, the LED specified in this data sheet falls into the class "moderate risk" (exposure time 0.25s). Under real circumstances (for exposure time, eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. As is also true when viewing other bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment and even accidents, depending on the situation.

For further information please contact ILS

The values contained in this data sheet can change due to technical innovations. Any such changes will be made without separate notification.